



ST111V

TABLETOP SKINNING MACHINE



MODEL



TECHNICAL DATA

FEATURE	DATA
Operators	1
Voltage range (1)	220- 480V 50-60Hz
Power (1)	0,55kW/3 phase
Controls	24V
LxWxH (2)	707 x 313 x 264 mm
Weight (3)	47 kg
Working width (2)	298 mm
Water usage (4)	-
Water connection	1/2"
Air usage	-
Air connection	-
Speed (5)	+/- 22 m per minute

(1) depending on requested voltage

(2) 1mm = 0,03937 inches

(3) 1kg = 2,20462 pounds

(4) spray system is optional if required

(5) $\frac{2200\text{cm/min}}{\text{length fillet (cm)} + 5\text{cm}} = \text{theoretical capacity}$

DESCRIPTION



Versatile tabletop skinning machine suitable for various fish species and sizes. Please check our website and product matrix on the main folder for more information. When ordering, please provide STEEN with the electrical specifications and water connection available. Also inform us which fish species (preferably the scientific name) you would like to process, each with their capacity and general length. Please indicate if you have any special requirements regarding the product.






Универсальная настольная машина для снятия шкуры подходит для различных видов и размеров рыбы. Для получения дополнительной информации, пожалуйста, посетите наш веб-сайт и посмотрите таблицу продуктов в основной папке. При заказе, пожалуйста сообщите STEEN о требуемых характеристиках электропитания и подсоединения воды. Также сообщите нам, какие виды рыбы (желательно научное название) вы хотели бы обрабатывать, планируемые объемы и основные размеры (длину) рыбы. Пожалуйста, укажите, есть ли у вас какие-либо особые требования к продукту.



多功能台式去皮机适合于各种大小的鱼和鱼片, 请查阅我们网站和产品列表以获得更多信息, 订货时, 请向STEEN公司说明电器规范和水源连接规格, 还有告诉我们您加工的是哪种鱼 (最好是学名, 每种鱼的产量和长度。请说明您对鱼是否有特殊要求。



FOOTPRINT



Due to the high degree of customization possibilities, technical data of the final product may vary.




OPTIONS



ST111V

TABLETOP SKINNING MACHINE



111/SC600MF

1



Converter 220V single phase

111/SC602

2



Table for machine at optimal height

111/SC603

3



Skin collector with(603) or without(611) water drainage

111/SC611

4

111/SC001A


5



Upper roller to close skinning gap for more safety

111/SC046A

6



Safety switch

111/SC018A8

7



Outfeed tray

111/SC045A

8



Guarded shielding

111/SC042A

9



Spray system

CUSTOMIZED

10



Tailor-made solution

Due to the high degree of customization possibilities, technical data of the final product may vary.